


## New POLIFLAP Grinding Wheel

For a perfect surface finish




- For use on textured surfaces.
- Abrasive and rubber flaps are easily replaceable.
- Excellently suited for surface finishing on stainless steels.

# POLIFLAP Grinding wheel

## Grinding wheel, abrasive flaps, rubber flaps

**POLIFLAP grinding wheel**



The POLIFLAP wheel consists of a shank-mounted (12 mm dia.) hub carrying an array of rubber flaps. For use, appropriate abrasive flaps must be fitted between their rubber counterparts. The combination arrangement of abrasive and rubber flaps results in a highly flexible tool.

**Application examples:**

- Redressing and restoration of surface textures
- Fine-grinding of radii, contours, curved areas or large surfaces
- Removal of fine secondary burr



- Removal of heat discoloration
- Surface cleaning

**Recommendation for use**


This product is used preferably on straight grinders and flexible shaft systems. On stainless steel, an optimum surface finish is obtained in the 1400 - 1700 r.p.m. speed range.

**Ordering note**

POLIFLAP grinding wheels are supplied without abrasive flaps. Please order abrasive flaps separately, specifying the desired grit size (refer to the table at center page).

Order No.	EAN 4007220	D x T [mm]	Shank dia. [mm]	Recom. speed [RPM]	Max. speed [RPM]		
PFL 17060/12	725405	170 x 60	12	1.500	3.500	1	590


**POLIFLAP abrasive flaps**





Abrasive flaps are available in eight different grit sizes (refer to the table below) for different visual effects.


Worn abrasive flaps can be easily replaced on the POLIFLAP wheel. A full set comprises 12 abrasive flaps (1 pack).

Please order a starter set and any additional sets of abrasive flaps separately.



Order No.	Grit size								B x L [mm]		
	60	80	100	120	150	180	220	320			
EAN 4007220											
PFL-SL A	725276	725283	725290	725306	725313	725320	725337	725344	60 x 75	12	100



**POLIFLAP rubber flaps**



The rubber flaps placed between any two abrasive flaps support the grinding action and flexibility of this tool.

Worn rubber flaps can be easily replaced on the POLIFLAP wheel. A full set comprises 12 rubber flaps (1 pack).



Order No.	EAN 4007220	B x L [mm]		
PFL-GL	725412	55 x 50	12	190